
# **TECNOCRYO**

### **GAS SUPPLY PANELS**



MATERIALS	
Body, bonnet	316L stainless steel barstock LHPI 800PS or chrome plated brass barstock LHPI 800PC
Diaphragm (regulator)	Hastelloy® * C276
Diaphragm (valve)	Elgiloy®**
Nozzle	316L stainless steel
Seat	PEEK
Seals O-ring	Viton®***(FKM)
Filter	SS 316L
Adjusting Knob	Aluminium

\* Hastelloy® is a registered trademark name of Haynes International, Inc \*\*Elgiloy® a registered trademark of Elgiloy Specialty Metals \*\*\*\* Viton® is a registered trademark of The Chemours Company

### LHPI 800P | HIGH PURITY SEMI-AUTOMATIC SWITCHOVER SUPPLY PANEL

The HPI 800P is a semi-automatic high purity switchover prevents downtime by automatically switching gas supply panel from the primary cylinder bank to the reserve cylinder bank. The user resets the primary bank by turning the knob. Outlet pressure is factory pre-set.

#### **APPLICATIONS:**


- Laboratory pressure control; •
- Research sample systems gases; •
- Component testing; •
- Petrochemical industry; •
- Emission monitoring systems;
- Controlled atmosphere;
- Service & test equipment.

#### FEATURES:


- Recommended for non-corrosive gases purity levels up to grade 6.0 (99.9999);
- Wall mounting panel and brackets included;
- Ready to install wall mounting panel;
- Metal steel diaphragm eliminates contamination • from diffusion or outgassing;
- Purge function and diaphragm shut-off valves for the . best results;
- Possible to connect 2 gas cylinders or gas cylinder . and a gas for purging operation;
- HPI 800PC chrome plated body, bonnet and fittings;
- HPI 800PS 316L ctainless steel body, bonnet and fittings; .
- 1x10<sup>-9</sup> mbar I/s He inboard helium leak rate to • maintain gas purity levels;
- Inlet / outlet 1/4" FNPT; .
- Maximum inlet pressure 300 bar (4350 psig); .
- Tested for use with oxygen. .

TECHNICAL DATA	
Panel type	Semi-automatic switchover supply panel
Regulator type	Single stage
Purity	Up to 6.0
Inlet pressure	Max. 300 bar (4350 psi)
Outlet pressure	2/4/10/20 bar (29/58/145/290 psi)
Purge function	Yes
Oxygen use	Suitable


## **GAS SUPPLY PANELS**



SPECIFICATION	
Inlet / outlet ports	1/4" NPT-F
Weight	4,8 kg
Temperature range	-30°C to +74°C







NOTE

TECNOCRYO www.tecnocryo.com